



Liquid-Filled Two-Piece Capsules Filling, Banding and Check Weighing Equipment at ACP

Qualicaps® capsule filling machines feature a compact size with easy conversion, highly accurate filling and the ability to handle a variety of dosage forms. Qualicaps® liquid-fill machines can accommodate a wide range of liquids, from mobile liquids to hot melts, with unique features such as proprietary hot-air purge and stacking cooling tower. Our F-40 will fill up to 40,000 capsules per hour at capsule sizes 00, 0EL, 0, 1, 2, 3, 4 and 5.



Qualicaps® capsule band-sealing equipment double-band sealing technique ensures that if an air bubble or unevenness occurs in the first band, it will be eliminated by the second application, making the HICAPSEAL a critical component for a leak-free product. Our S-40 will band-seal up to 40,000 capsules per hour at capsule sizes 00, 0EL, 0, 1, 2, 3, 4 and 5.



Qualicaps® capsule weight inspection equipment provides high speed and accurate processing for 100% weight inspection. Our CWI-40 will weight sort up to 40,000 capsules per hour at capsule sizes 00, 0EL, 0, 1, 2, 3, 4 and 5.